


DTE801



Compact RFID device

DTRUHFE HLRWPNUS04



Application	
Radio approval for	EU/RED; India
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under "Downloads".
Electrical data	
Operating voltage [V]	19.2...28.8 DC
Current consumption [mA]	500
Power consumption [W]	8.6
Protection class	III
Operating frequency [MHz]	865...868 (ETSI)
RFID standard	EPC Class1 GEN2/ISO 18000-63
Transmission power ERP [mW]	120; (maximum: 200 mW)
Outputs	
Max. current load per output [mA]	100; (max.)
Interfaces	
Communication interface	Ethernet
Ethernet - PROFINET	
Protocol	PROFINET
Usage type	data transmission
Ethernet - TCP/IP	
Protocol	TCP/IP
Factory settings	IP address: 192.168.0.79
	subnet mask: 255.255.255.0
	gateway IP address: 192.168.0.100
Usage type	parameter setting

DTE801



Compact RFID device

DTRUHFE HLRWPNUS04

Operating conditions		
Ambient temperature	[°C]	-20...55
Note on ambient temperature		with mounting plate and cooling element: -20...60 °C
Storage temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals		
Shock resistance	IEC 60028-2-27	40 g (6 ms) / bump
		50 g (11 ms) / single shock
Vibration resistance	EN 60068-2-6	2 g (10...150 Hz)
MTTF	[years]	58

Mechanical data		
Weight	[g]	705.8
Dimensions	[mm]	113 x 118.6 x 50
Materials		housing: aluminium; PBT / PC; stainless steel

Displays / operating elements		
Display	power supply	1 x LED, green
	LED bar display	4 x LED, yellow number of tags in the field
	status	2 x LED, green/red fieldbus interface
	status	2 x LED, green/yellow Ethernet

Remarks		
Pack quantity		1 pcs.

Electrical connection - Ethernet


Connector: 2 x M12; coding: D



ETH1 / ETH2		
1		TD+
2		RD+
3		TD-
4		RD-

Electrical connection - power supply

Connector: 1 x M12; coding: A



DTE801



Compact RFID device

DTRUHFE HLRWPNUS04

PWR	
1	L+
2	digital input/output 2
3	L-
4	digital input/output 1
5	not used