


Flow monitor

SCR12ABAFNKG/PH

Article no longer available - archive entry

Alternative articles: SI5001 + E40096

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Process connection	G 1/2 external thread

Application

Media	Liquids
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Electrical data

Operating voltage [V]	20...36 DC
Current consumption [mA]	< 45
Reverse polarity protection	yes
Power-on delay time [s]	< 20

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Outputs

Total number of outputs	1
Output signal	switching signal
Electrical design	NPN
Number of digital outputs	1

ST3620



Flow monitor

SCR12ABAFNKG/PH

Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	400	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Setting range	[cm/s]	3...300	
Greatest sensitivity	[cm/s]	3...60	
Accuracy / deviations			
Temperature gradient	[K/min]	15	
Response times			
Response time	[s]	1...10	
Software / programming			
Adjustment of the switch point		potentiometer	
Operating conditions			
Ambient temperature	[°C]	-20...80	
Protection		IP 67	
Mechanical data			
Dimensions	[mm]	60 x 41 x 83	
Materials		PBT-GF20	
Materials (wetted parts)		stainless steel (1.4305 / 303)	
Process connection		G 1/2 external thread	
Displays / operating elements			
Display	function	11 x LED	
Accessories			
Items supplied		sealings: 2 x AMF 30	
		screwdrivers	
Remarks			
Pack quantity		1 pcs.	

ST3620





Flow monitor

SCR12ABAFNKG/PH

Electrical connection

Cable: 2 m, PUR; 3 x 0.5 mm²

Connection



BN =
BU =
BK =

Core colours :
brown
blue
black