


RU-0635-I24/L2



Technical drawing of a circular part with a 120-degree sector removed. The drawing includes a top view and a side view. The top view shows a circular part with a diameter of 42 (Ø42) and a central hole. Three smaller holes are arranged in a triangle. The side view shows a thickness of 17 and a 30-degree angle. The part has a 120-degree sector removed, indicated by a curved arrow and the angle 120°.



- 1 位置マーク
2 M4 深さ 5 mm




製品特性		
分解能		635 分解能
シャフト		ソリッドシャフト
シャフト径	[mm]	6
電氣的仕様		
使用電源電圧範囲	[V]	DC 10～30
消費電流	[mA]	150
出力		
電氣仕様		HTL
出力開閉電流	[mA]	50
応答周波数	[kHz]	300
短絡保護機能タイプ		< 60 s
A、Bの位相差	[°]	90
測定範囲 / 設定範囲		
分解能		635 分解能
使用環境条件		
使用周囲温度	[°C]	-20～85
保存温度	[°C]	-30～100
最大相対湿度	[%]	98
保護構造		IP 64

RU6020



インクリメンタル式エンコーダ ソリッドシャフト

RU-0635-I24/L2

試験 / 認証		
衝撃耐性		100 (x 9.81 m/s²) (6 ms)
振動耐性		10 (x 9.81 m/s²) (55~2000 Hz)
機械的仕様		
外形寸法	[mm]	Ø 58 / L = 46
材質		アルミニウム
機械的最大許容回転数	[U/min]	12000
始動トルク	[Nm]	1
トルク基準温度	[°C]	20
シャフト		ソリッドシャフト
シャフト径	[mm]	6
材質		ステンレス1.4104(SUS430F)
スラスト荷重(軸端)	[N]	10
ラジアル荷重(軸端)	[N]	20
フランジ形状		シンクロフランジ
電気接続		
ケーブル: 2 m, PUR, 軸方向		
茶	A	
緑	A 反転	
灰	B	
桃	B 反転	
赤	原点信号	
黒	原点信号 反転	
青	L+ センサ	
白	0V センサ	
茶/緑	L+ (Up)	
白/緑	0V (Un)	
紫	エラー 反転	
シールド	外装	
特性図等		
出力信号		
回転方向: 時計回り(シャフト側から見て)		