


Fibre optic through-beam sensor

FE-11-EPA-M4/F16X0,265/2M



Application

Function principle	Through-beam sensor
Application	Small bending radius

Detection zone

Range with fibre-optic amplifier type	OB50; OBF; OCF; OO50
---------------------------------------	----------------------

OB50

Range of fibre optics [mm]	150
----------------------------	-----

OBF

Range of fibre optics [mm]	210
----------------------------	-----

OCF (High Power)

Range of fibre optics [mm]	2590
----------------------------	------

OO50

Range of fibre optics [mm]	800
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-40...70
--------------------------	----------

Mechanical data

Weight [g]	47
Version of sensing head	straight
Sensing head thread	M4

E20615



Fibre optic through-beam sensor

FE-11-EPA-M4/F16X0,265/2M

Sensing head length	[mm]	15
Total length	[mm]	2000
Min. bending radius	[mm]	9
Fibre arrangement		
Core diameter	[mm]	16 x 0.25
Fibre material		PMMA
Fibre head material		aluminium
Fibre sheath material		PE

Accessories

Items supplied	hexagon nuts: 4 x M4 tooth lock washers: 4
Accessories (optional)	Cutter for fibre optics:, E20600

Remarks

Pack quantity	1 pcs.
---------------	--------