

Technical drawing of the LED module (Fig. 1). The drawing shows a side view of the module with various dimensions. The total length is 98. The distance from the left end to the center of the LED is 82. The distance from the center of the LED to the center of the mounting holes is 55. The distance between the centers of the mounting holes is 42. The distance from the center of the mounting holes to the right end is 8. The diameter of the mounting holes is 4. The distance from the left end to the center of the mounting holes is 42. The distance from the center of the mounting holes to the right end is 8. The diameter of the mounting holes is 4. The distance from the left end to the center of the LED is 82. The total length is 98. The drawing also shows a cross-section of the module with a diameter of 28 and a thread of M18x1. The LED is labeled 'LED' and the mounting holes are labeled '4'.



전기적 디자인	PNP
출력 기능	N.O.
검출간격 [mm]	8
하우징	나선형 홈이 파여진 형태
크기 [mm]	M18 x 1

동작 전압	[V]	10...36 DC
전류소모	[mA]	15; (24 V)
보호 클래스		II
양극성 전환 방지		yes

전기적 디자인	PNP
출력 기능	N.O.
최대 전압강하 스위칭 출력 DC [V]	2,5
스위칭 출력 DC의 영구적 전류 등급 [mA]	250
스위칭 주파수 DC [Hz]	300
쇼트방지	yes
쇼트방지 타입	펄스
과부하 방지	yes



유도형 근접센서

IGA3008-BPKG/TS-600-APS

범위		
검출간격	[mm]	8
실제 감지범위 Sr	[mm]	$8 \pm 10 \%$
작업거리	[mm]	0...6,5
정확성 / 편차		
교정 계수		금속: 1 / 스텐레스: 0,7 / 황동: 0,4 / 알루미늄: 0,3 / 구리: 0,2
히스테리시스	[Sr 의 %]	1...15
접합점 드리프트	[Sr 의 %]	-10...10
작동 조건		
주변온도	[°C]	-25...80
보호등급		IP 65
테스트 / 인증서		
EMC	EN 60947-5-2	
	EN 55011	B 등급
기계적 데이터		
무게	[g]	154
하우징		나선형 홈이 파여진 형태
설치방식		돌출형 마운팅
크기	[mm]	M18 x 1
스레드 지정		M18 x 1
재질		황동 흰색 청동 코팅; CO-PC
디스플레이 / 작동 요소		
디스플레이	스위칭 상태	1 x LED, 황색
액세서리		
구성 부품		잠금 너트: 2
비고		
포장당		1 갯수
전기적 연결 - 플러그		

커넥터: 1 x Ø 28 mm; 코딩: A



IG5579



유도형 근접센서

IGA3008-BPKG/TS-600-APS

연결부

