




IO-Link display

IO-LINK MASTER DISPLAY 1,44



Application		
Special feature	Gold-plated contacts	
Application	display of all process values of the sensors connected to the same master	
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 47
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Software / programming		
Parameter setting options	display, indication	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud); COM3 (230,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	no	
Required master port type	A	
Min. process cycle time	[ms]	11.2
Supported DeviceIDs	Type of operation	DeviceID
	default	824
Operating conditions		
Ambient temperature	[°C]	0...60



IO-Link display

IO-LINK MASTER DISPLAY 1,44

Storage temperature	[°C]	-20...80
Protection		IP 65; IP 67

Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-4	
Shock resistance	DIN EN 60068-2-27	5 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...50 Hz)
MTTF	[years]	398

Mechanical data

Weight	[g]	171.5
Materials		stainless steel (316L/1.4404); PC; PBT-GF30; PPS; FKM;

Displays / operating elements

Display		colour display 1,44", 128 x 128 pixels
		2 x LED, yellow

Remarks


Pack quantity		1 pcs.
---------------	--	--------

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



colours to DIN EN 60947-5-2
Core colours :
BK = black
BN = brown
BU = blue