




Inductive sensor

IF-3002-ANOG

Article no longer available - archive entry

Alternative articles: IF5321

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	2
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 71

Electrical data

Operating voltage [V]	10...55 DC
Current consumption [mA]	7; (24 V)
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	400
Switching frequency DC [Hz]	700
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	2
Real sensing range S_r [mm]	$2 \pm 10 \%$
Operating distance [mm]	0...1.6

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of S_r]	1...15
Switch point drift [% of S_r]	-10...10

IF5001



Inductive sensor

IF-3002-ANOG

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Mechanical data

Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M12 x 1 / L = 71
Thread designation		M12 x 1
Materials		PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied		lock nuts: 2
----------------	--	--------------


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.34 mm²

Connection



BN = Core colours :
brown
BU = blue
BK = black