


Inductive AS-Interface sensor

IGA2012-ASI /US-100

Article no longer available - archive entry

Alternative articles: IGC235

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	AS-i
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	12
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 80

Application

Special feature	Optical setting aid
-----------------	---------------------

Electrical data

Operating voltage [V]	26.5...31.6 DC
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	AS-i
Output function	normally open / normally closed; (selectable)
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	12
Real sensing range Sr [mm]	12 ± 10 %
Operating distance [mm]	0...9.7

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.72 / aluminium: 0.42 / copper: 0.4
Hysteresis [% of Sr]	5



Inductive AS-Interface sensor

IGA2012-ASI /US-100

Switch point drift	[% of Sr]	-10...10
--------------------	-----------	----------

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

AS-i classification

AS-i I/O configuration	[hex]	1				
AS-i ID code	[hex]	1				
AS-i certificate		21701				
Assignment of the data bits		Designation	switching signal	safe zone	readiness for operation	not used

Mechanical data

Housing	threaded type
Mounting	non-flush mountable
Dimensions [mm]	M18 x 1 / L = 80
Thread designation	M18 x 1
Materials	brass white bronze coated; PC

Displays / operating elements

Display	switching status	1 x LED, yellow
	unsafe zone	1 x LED, red sensor coil wire break, sensor coil short circuit Sr: 0...10 % (< 10 Hz) Sn: 80...115 % (< 10 Hz)
Optical setting aid	yes	

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Remarks	Assured range: approx. 10...80 % of Sn
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A





Inductive AS-Interface sensor

IGA2012-ASI /US-100

Connection

