


KF5002



Capacitive sensor

KFA3080NBPKG/NI/US



- 1 LED 4 x 90°
2 potentiometer



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	3...12
Housing		threaded type
Dimensions	[mm]	M12 x 1 / L = 61
Application		
Media		dry bulk material; liquids
Electrical data		
Operating voltage	[V]	10...36 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 12
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	50
Short-circuit proof		yes
Overload protection		yes
Detection zone		
Sensing range	[mm]	3...12
Sensing range adjustable		yes
Factory setting sensing range	[mm]	8
Real sensing range Sr	[mm]	8 ± 10 %
Accuracy / deviations		
Correction factor		glass: 0.6 / water: 1 / ceramics: 0.5 / PVC: 0.4
Hysteresis	[% of Sr]	1...15

KF5002



Capacitive sensor

KFA3080NBPKG/NI/US

Switch point drift	[% of Sr]	-20...20
--------------------	-----------	----------

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 65
Increased immunity		yes

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	634

Mechanical data

Weight	[g]	39.2
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M12 x 1 / L = 61
Thread designation		M12 x 1
Materials		stainless steel (316L/1.4404); PEEK

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection

