



Article no longer available - archive entry

No scale drawing available



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Dimensions [mm]	M30 x 1.5

Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 3
Reverse polarity protection	yes

Outputs

Total number of outputs	1
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Short-time current rating of switching output [mA]	250
Short-circuit proof	yes
Overload protection	yes


DI5008



Compact evaluation unit for speed monitoring

DIA3010-ZPKG/200/2sAUE/2M/US

Detection zone		
Sensing range	[mm]	10
Sensing range adjustable		no
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Response times		
Start-up delay	[s]	2
Max. damping frequency	[Imp/min]	15000
Software / programming		
Adjustment of the switch point		fixed
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Mechanical data		
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Materials		brass special coating; PBT
Tightening torque	[Nm]	50
Displays / operating elements		
Display	switching status	1 x LED, green
Electrical connection		
Cable: 2 m, PUR		
Connection		



Connector: 1 x M12