


SF5702



Flow sensor for connection to an evaluation unit

SFD10ADT /US-100



1 internal thread M18 x 1,5



Product characteristics

Probe length L	[mm]	93
Process connection		M18 x 1,5 internal thread

Application

Media		Liquids; Gases; aggressive media
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	100

Electrical data

Connection to control monitor		VS3000
-------------------------------	--	--------

Measuring/setting range

Probe length L	[mm]	93
----------------	------	----

Liquids

Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60

Gases

Setting range	[cm/s]	200...3000
Greatest sensitivity	[cm/s]	200...800

Accuracy / deviations

Temperature gradient	[K/min]	300
----------------------	---------	-----

Response times

Response time	[s]	1...10
---------------	-----	--------

Operating conditions

Storage temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	10 g (55...2000 Hz)
MTTF	[years]	8393.77

SF5702



Flow sensor for connection to an evaluation unit


SFD10ADT /US-100

Mechanical data		
Weight	[g]	68
Housing		for adapter
Dimensions	[mm]	M18 x 1.5
Thread designation		M18 x 1.5
Materials		titanium (3.7035); EPDM; ULTEM
Materials (wetted parts)		titanium (3.7035); O-ring: FKM 80 Shore A
Process connection		M18 x 1,5 internal thread


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



Connection



Core colours :
BN = brown
BU = blue
BK = black
WH = white
GY = grey