


Connecting cable with socket

ADOGH042MSS0005A04

Article no longer available - archive entry

Alternative articles: EVC645

When selecting an alternative article and accessories please note that technical data may differ!



Application

Special feature	Halogen-free
-----------------	--------------

Electrical data

Operating voltage	[V]	10...30 DC
-------------------	-----	------------

Operating conditions

Ambient temperature	[°C]	-25...80
---------------------	------	----------

Protection	IP 67
------------	-------

Mechanical data

Weight	[g]	163
--------	-----	-----

Dimensions	[mm]	15 x 15 x 47
------------	------	--------------

Materials	PUR transparent
-----------	-----------------

Moulded-body material	PUR, transparent
-----------------------	------------------

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Remarks

Pack quantity	1 pcs.
---------------	--------

E10827



Connecting cable with socket

ADOGH042MSS0005A04

Electrical connection


Cable: 5 m, PUR, Halogen-free, black, Ø 4.8 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: PUR, transparent; Tightening torque: 0.5 Nm



Connection



BN =	Core colours :
BK =	brown
BU =	black
WH =	blue
	white