




Fibre optic diffuse reflection sensor

FT-11-EPA-Q-/F2x1/2M



1 reference edge

Application

Special feature	Background suppression
Function principle	Diffuse reflection sensor
Application	Small bending radius

Detection zone

Range with fibre optic amplifier type	OB50; OBF; OCF
Background suppression available	yes

OB50

Range fibre optics [mm]	6
-------------------------	---

OBF

Range fibre optics [mm]	10
-------------------------	----

OCF (High Power)

Range fibre optics [mm]	20
-------------------------	----

Operating conditions

Ambient temperature [°C]	-40...70
--------------------------	----------

Mechanical data

Weight [g]	54
Sensing head height [mm]	5
Sensing head width [mm]	35
Sensing head length [mm]	23
Probe dimensions [mm]	5 x 35 x 23
Total length [mm]	2000
Min. bending radius [mm]	10
Fibre arrangement	●
Core diameter [mm]	2 x 1
Fibre material	PMMA
Fibre head material	aluminium
Fibre sheath material	PE

E20756



Fibre optic diffuse reflection sensor

FT-11-EPA-Q-/F2x1/2M

Accessories	
Accessories (optional)	Cutter for fibre optics:, E20600
Remarks	
Pack quantity	1 pcs.