

# E20365




## Fibre optic through-beam sensor

FE-00-A-A-R3/2m

Article no longer available - archive entry

Alternative articles: E20366  
When selecting an alternative article and accessories please note that technical data may differ!



| Application                           |                     |
|---------------------------------------|---------------------|
| Function principle                    | Through-beam sensor |
| Detection zone                        |                     |
| Range with fibre-optic amplifier type | OKF; OUF            |
| OKF                                   |                     |
| Range of fibre optics [mm]            | 96                  |
| OUF                                   |                     |
| Range of fibre optics [mm]            | 96                  |
| Operating conditions                  |                     |
| Ambient temperature [°C]              | -40...290           |
| Mechanical data                       |                     |
| Version of sensing head               | angled              |
| Sensing head diameter [mm]            | 3                   |
| Sensing head length [mm]              | 10                  |
| Total length [mm]                     | 2000                |

E20365



Fibre optic through-beam sensor

FE-00-A-A-R3/2m

|                       |              |    |
|-----------------------|--------------|----|
| Min. bending radius   | [mm]         | 20 |
| Materials             | Adapter: ABS |    |
| Fibre material        | glass        |    |
| Fibre head material   | aluminium    |    |
| Fibre sheath material | aluminium    |    |
| Remarks               |              |    |
| Pack quantity         | 1 pcs.       |    |