


Fibre optic diffuse reflection sensor

FT-11-EPV-Q3/F2x1/2m



1 fixing holes

Application

Function principle

Diffuse reflection sensor

Application

For use in industrial environments

Detection zone

Range with fibre-optic
amplifier type

OBF; OO50; OCF

OBF

Range of fibre optics

[mm]

70

OO50

Range of fibre optics

[mm]

150

OCF (High Power)

Range of fibre optics

[mm]

530

Operating conditions

Ambient temperature

[°C]

-40...70

Mechanical data

Weight

[g]

45.2

E21312



Fibre optic diffuse reflection sensor

FT-11-EPV-Q3/F2x1/2m

Version of sensing head		angled
Sensing head height	[mm]	3
Sensing head width	[mm]	11
Sensing head length	[mm]	15
Probe dimensions	[mm]	3 x 11 x 15
Total length	[mm]	2000
Min. bending radius	[mm]	2
Fibre arrangement		⊙⊙
Core diameter	[mm]	1
Fibre material		PMMA
Fibre head material		stainless steel (303/1.4305)
Fibre sheath material		PE

Accessories

Items supplied	hexagon nuts: 2 x M2, stainless steel
Accessories (optional)	Cutter for fibre optics:, E20600

Remarks

Pack quantity	1 pcs.
---------------	--------