


Inductive sensor

IVE4015-CPKG/US-100-DPA

Article no longer available - archive entry

Alternative articles: IV5003

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	15
Housing	rectangular
Dimensions [mm]	40 x 40 x 118

Electrical data

Operating voltage [V]	10...60 DC
Current consumption [mA]	20; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	complementary



Inductive sensor

IVE4015-CPKG/US-100-DPA

Max. voltage drop switching output DC	[V]	3
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	150
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone		
Sensing range	[mm]	15
Real sensing range S_r	[mm]	$15 \pm 10 \%$
Operating distance	[mm]	0...12.1

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of S_r]	1...15
Switch point drift	[% of S_r]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...50
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	40 x 40 x 118
Materials		PBT

Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Remarks		
Remarks		5 positions of the active zone possible
		Cable gland (E11270) to be ordered separately
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A





Inductive sensor

IVE4015-CPKG/US-100-DPA

Connection

