


M9H206



Cylinder sensor

M9B3002BBPKG/B/AM/500/0,5M/US



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1.8
Housing	threaded type
Dimensions [mm]	M14 x 1.5 / L = 41

Application

Application	hydraulic cylinders
Media	detects ferrous metals
Min. bursting pressure [bar]	2000
Pressure rating [bar]	500

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 23
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1.6
Max. leakage current [mA]	0.1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit proof	yes
Overload protection	yes

Detection zone

Sensing range [mm]	1.8
Real sensing range Sr [mm]	1.8 ± 10 %

M9H206



Cylinder sensor

M9B3002BBPKG/B/AM/500/0,5M/US

Operating distance	[mm]	0...1.46
Accuracy / deviations		
Hysteresis	[% of Sr]	< 15
Switch point drift	[% of Sr]	10
Repeatability	[% of Sr]	10
Operating conditions		
Pressure peak	[bar]	1000
Ambient temperature	[°C]	-25...85
Protection		IP 65; IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
	DIN ISO 11452-5	100 V/m
Vibration resistance	EN 60068-2-6 Fc	20 g 50 sweep cycles, 1 octave per minute, in 3 axes / 10...3000 Hz -20...50 °C
Shock resistance	EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes / -40...85 °C
Continuous shock resistance	EN 60068-2-27 Ea	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes / -20...50 °C
MTTF	[years]	925
Mechanical data		
Weight	[g]	72.8
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M14 x 1.5 / L = 41
Thread designation		M14 x 1.5
Materials		housing: stainless steel stainless steel (316L/1.4404); O-ring: FKM
Tightening torque	[Nm]	< 25
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.

M9H206



Cylinder sensor

M9B3002BBPKG/B/AM/500/0,5M/US


Electrical connection - plug

Cable: 0.5 m, PUR

Connector: 1 x M12; coding: A; Locking: knurled nut, rotatable



Connection



Diagrams and graphs

