




Control monitor for flow sensors

VS0200/200VAC

Article no longer available - archive entry

Alternative articles: SN0150  
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application		Flow monitoring
Electrical data		
Operating voltage	[V]	< 200 AC
Max. power consumption	[VA]	3
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design		relay
Contact rating		4 A, 250 V AC
Switching function flow monitoring		relay energised when flow is present
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 40
Protection rating terminals		IP 20
Mechanical data		
Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110


# SN0117



## Control monitor for flow sensors

VS0200/200VAC

Materials	plastics	
Displays / operating elements		
Display	function	11 x LED
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
terminals: 16 x ...2.5 mm²		
Connection		



- 1: Relais Flow monitoring  
Core colours :
- BN = brown  
BU = blue  
BK = black  
WH = white  
GY = grey