
SR5906

Control monitor for flow sensors









Application				
Application		Flow monitoring; Wire monitoring		
Electrical data				
Frequency AC	[Hz]	4763		
Operating voltage tolerance	[%]	-1510		
Operating voltage	[V]	90240 AC		
Max. power consumption	[VA]	3.5		
Protection class		II		
Reverse polarity protection		no		
Power-on delay time	[s]	10		
Number of channels		1		
Outputs				
Electrical design		relay		
Contact rating		3 A (250 V AC / 30 V DC); (switching cycles at 3 A load: 100.000; type of switch-off: normally open)		
Switching cycles (mechanical)		20_Millionen		
Switching function flow monitoring		output switches when flow is present: ON for output function = normally open / OFF for output function = normally closed		
Short-circuit protection		no		
Overload protection		no		

SR5906

Control monitor for flow sensors





Software / programming				
Adjustment of the switch point	pushbutton			
Operating conditions				
Ambient temperature [°C]	-2060			
Protection	IP 67; (with sensor attached)			
Tests / approvals				
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD		
	EN 61000-4-3 HF radiated	10 V/m		
	EN 61000-4-4 Burst	2 kV		
	EN 61000-4-6 HF conducted	10 V		
Shock resistance	DIN IEC 68-2-27	30 g (6 ms)		
Vibration resistance	DIN IEC 68-2-6	2 g (552000 Hz)		
MTTF [years]	209			
Mechanical data				
Weight [g]	244.5			
Materials	stainless steel (316L/1.4404); stainless steel (304/1.4301); PC; PBT-GF20; EPDM/X; brass			
Displays / operating elements				
Display	function	LED, bar graph		
	switching status	LED, orange flash in case of wire break		
Electrical connection				
Required protection	miniature fuse to IEC60127-2 sheet 1; \leq 5 A; fast acting			
Remarks				
Remarks	Connection for flow sensor without short-circuit protection / reverse polarity protection.			
	The flow sensor must be directly connected to the control monitor.			
	A connection by means of extension cables is not allowed.			
	Recommendation Check the safe functioning of the unit after a short circuit.			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x 1/2"; coding: C				



3


SR5906

Control monitor for flow sensors

SRM12XXAKOW/LS-100-IRF



Connection



n.c. = not used

Note miniature fuse to IEC60127-2 sheet $1 \le 5$ A fast acting

Caution no protective insulation between relay circuit and supply voltage