



Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P

Article no longer available - archive entry

Alternative articles: PI1696

When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
- 2 programming button



EHEDG Certified



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	-0.13...2.5 bar	-1.8...36.3 psi	-13...250 kPa
Process connection	threaded connection G 1 external thread		

Application

Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	freely rotatable housing 350°		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	50 bar	725 psi	5000 kPa
Pressure rating	20 bar	290 psi	2000 kPa
Type of pressure	relative pressure		
No dead space	yes		



Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P

Electrical data			
Operating voltage	[V]	20...30 DC	
Current consumption	[mA]	< 60	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	0.2	
Integrated watchdog		yes	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1	
Outputs			
Total number of outputs		2	
Output signal		switching signal; analogue signal; (configurable)	
Electrical design		PNP/NPN	
Number of digital outputs		2	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	< 170	
Number of analogue outputs		1	
Analogue current output	[mA]	4...20; (scalable 1:4)	
Max. load	[Ω]	(Ub - 10 V) / 20 mA	
Analogue voltage output	[V]	0...10; (scalable 1:4)	
Min. load resistance	[Ω]	2000	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range	-0.13...2.5 bar	-1.8...36.3 psi	-13...250 kPa
Set point SP	-0.11...2.5 bar	-1.6...36.3 psi	-11...250 kPa
Reset point rP	-0.12...2.49 bar	-1.7...36.2 psi	-12...249 kPa
Analogue start point	-0.13...1.88 bar	-1.8...27.2 psi	-13...188 kPa
Analogue end point	0.5...2.5 bar	7.3...36.3 psi	50...250 kPa
In steps of	0.01 bar	0.1 psi	1 kPa
Accuracy / deviations			
Repeatability	[% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	[% of the span]	< ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)	
Linearity deviation	[% of the span]	< ± 0,5; (Turn down 1:1)	
Hysteresis deviation	[% of the span]	< ± 0,1; (Turn down 1:1)	
Long-term stability		< ± 0,1; (Turn down 1:1; per year)	



Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P

[% of the span]		
Temperature coefficient zero point		< ± 0,1; (0...80 °C)
[% of the span / 10 K]		
Temperature coefficient span		< ± 0,2; (0...80 °C)
[% of the span / 10 K]		
Response times		
Response time	[ms]	< 3
Damping process value dAP	[s]	0...4
Damping for the analogue output dAA in steps	[s]	0 - 0,1 - 0,5 - 2
Max. response time analogue output	[ms]	3
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span	
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Materials	stainless steel (316L/1.4404); PBT; PC; PEI; EPDM/X; FKM	
Materials (wetted parts)	stainless steel (316L/1.4404); ceramics (99.9 % Al2O3); PTFE	
Min. pressure cycles	100 million	
Process connection	threaded connection G 1 external thread	
Displays / operating elements		
Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display
Display unit	bar; psi; kPa	
Remarks		
Remarks	The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.	
Pack quantity	1 pcs.	



Flush pressure sensor with display

PI-2,5-REA01-MFRKG/US/ /P

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1
OUT2

switching output
switching output
analogue output