


PTU504



Pressure transmitter

PT-010-SEG14-A-ZVG/US



1 Sealing



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1		
Measuring range	0...10 bar	0...1000 kPa	0...1 MPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)		

Application

Application	for mobile applications	
Media	liquids and gases	
Medium temperature [°C]	-40...125	
Min. bursting pressure	300 bar	30 MPa
Pressure rating	25 bar	2.5 MPa
Note on pressure rating	static	
Vacuum resistance [mbar]	-1000	
Type of pressure	relative pressure	

Electrical data

Operating voltage [V]	8...32 DC		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	< 0.1		

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	(U _b - 8 V) / 21,5 mA; @8V = 0 Ω; @12V max. 200 Ω; @24V max. 750 Ω



Pressure transmitter

PT-010-SEG14-A-ZVG/US

Short-circuit proof		yes	
Overload protection		yes	
Measuring/setting range			
Measuring range		0...10 bar	0...1000 kPa 0...1 MPa
Accuracy / deviations			
Repeatability [% of the span]		< ± 0,05; (with temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]		< ± 0,8; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)	
Linearity deviation [% of the span]		< ± 0,25 (BFSL) / < ± 0,5 (LS)	
Hysteresis deviation [% of the span]		< ± 0,2	
Long-term stability [% of the span]		< ± 0,1; (per 6 months)	
Temperature coefficient zero point [% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)	
Temperature coefficient span [% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)	
Response times			
Step response time analogue output [ms]		2	
Operating conditions			
Ambient temperature [°C]		-40...100	
Storage temperature [°C]		-40...100	
Protection		IP 67; IP 69K	
Tests / approvals			
EMC		compliant with UN ECE R10, rev. 5 ISO 11452-2 DIN EN 61326-1	(E1 compliant) 100 V/m
Shock resistance		DIN EN 60068-2-27	500 g (1 ms)
Vibration resistance		DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]		711	
UL approval		UL Approval no. File number UL	J070 E174189
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight [g]		57.3	
Materials		stainless steel (630/1.4542/17-4 PH); stainless steel (316L/1.4404); PEI	
Materials (wetted parts)		stainless steel (630/1.4542/17-4 PH)	
Min. pressure cycles		60 million; (at 1.2 times nominal pressure)	
Tightening torque [Nm]		25...35; (recommended tightening torque; depends on lubrication, seal and pressure rating)	
Process connection		threaded connection G 1/4 external thread (DIN EN ISO 1179-2)	
Process connection sealing		HNBR (DIN EN ISO 1179-2)	
Restrictor element integrated		yes	



Pressure transmitter

PT-010-SEG14-A-ZVG/US

Remarks


Remarks	BFSL = Best Fit Straight Line
	LS = limit value setting
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A




Connection



OUT analogue output
 colours to DIN EN 60947-5-2
 Core colours :
BN = brown
WH = white

Diagrams and graphs

characteristic load curve of current output



1: Max. load
2: min. load