


Fibre optic through-beam sensor

FE-00-P-A-M4/1M

Article no longer available - archive entry



Application

Function principle	Through-beam sensor
--------------------	---------------------

Detection zone

Range with fibre-optic amplifier type	OKF; OUF
---------------------------------------	----------

OKF

Range of fibre optics [mm]	120
----------------------------	-----

OUF

Range of fibre optics [mm]	120
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Version of sensing head	straight
-------------------------	----------

Sensing head thread	M4
---------------------	----

Sensing head length [mm]	15
--------------------------	----

Total length [mm]	1000
-------------------	------

Min. bending radius [mm]	10
--------------------------	----

Materials	Adapter: PPE
-----------	--------------

Fibre material	glass
----------------	-------

E20092



Fibre optic through-beam sensor

FE-00-P-A-M4/1M

Fibre head material	aluminium
Fibre sheath material	PVC
Remarks	
Pack quantity	1 pcs.