
ST1204

Flow sensor for connection to an evaluation unit

STM12ABB/US-100-H

Article no longer available - archive entry



Product characteristics		
Process connection		M12 x 1
Application		
Application		high-temperature range
Media		Liquids; Gases
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	30
Liquids		
Application		high-temperature range
Medium temperature	[°C]	-25...80
Gases		
Medium temperature	[°C]	-25...80
Electrical data		
Connection to control monitor		VS 0100
Measuring/setting range		
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Gases		
Setting range	[cm/s]	5...1500
Accuracy / deviations		
Temperature gradient	[K/min]	15
Response times		
Response time	[s]	1...10
Liquids		
Response time	[s]	1...10
Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67

ST1204

Flow sensor for connection to an evaluation unit

STM12ABB/US-100-H

Mechanical data		
Housing		threaded type
Dimensions	[mm]	M12 x 1
Thread designation		M12 x 1
Materials		stainless steel (1.4571/316Ti)
Process connection		M12 x 1


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white