




AS-Interface PROFIBUS DP gateway with PLC

ContrE M4 1Mstr DPV1+ET

Article no longer available - archive entry

Alternative articles: AC1411
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application		decentralised controller
Electrical data		
Operating voltage	[V]	24 DC
Insulation rating	[V]	500
Current consumption	[mA]	< 400
Max. current consumption from AS-i	[mA]	10
Max. power consumption	[VA]	10
Number of AS-i masters		1
Electrical separation		yes
Interfaces		
Communication interface		RS232; Ethernet; PROFIBUS



AS-Interface PROFIBUS DP gateway with PLC

ContrE M4 1Mstr DPV1+ET

Ethernet - CAA		
Protocol	CAA	
Ethernet - Modbus TCP		
Transmission rate	10 MBaud; 100 MBaud	
Connector type	RJ45	
Protocol	Modbus TCP	
Usage type	programming	
PROFIBUS		
Transmission rate	12 MBaud	
Protocol	Profibus DP	
Usage type	data transmission	
RS232		
Number of R232 interfaces	1	
Transmission rate	9600...115200 Baud	
Connector type	RJ11	
Usage type	programming	
Note on interfaces	electrically isolated	
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Protection	IP 20	
AS-i classification		
AS-i version	2.11; 3.0	
AS-i master profile	M4	
Mechanical data		
Weight	[g]	588.5
Housing	housing for DIN rail mounting	
Materials	aluminium; steel sheet galvanised	
Displays / operating elements		
Display	function	2 x LED, red
		2 x LED, green
		3 x LED, yellow
		full graphic LCD display
Remarks		
Pack quantity	1 pcs.	



AS-Interface PROFIBUS DP gateway with PLC

ContrE M4 1Mstr DPV1+ET

Electrical connection

Connection

