


## Inductive sensor

IGA2008-BBOA/20m

Article no longer available - archive entry



### Product characteristics

|                 |      |                  |
|-----------------|------|------------------|
| Output function |      | normally closed  |
| Sensing range   | [mm] | 8                |
| Housing         |      | threaded type    |
| Dimensions      | [mm] | M18 x 1 / L = 80 |

### Electrical data

|                             |     |                |
|-----------------------------|-----|----------------|
| Operating voltage           | [V] | 20...250 AC/DC |
| Protection class            |     | II             |
| Reverse polarity protection |     | no             |

### Outputs

|                                                 |      |                                                 |
|-------------------------------------------------|------|-------------------------------------------------|
| Output function                                 |      | normally closed                                 |
| Max. voltage drop switching output DC           | [V]  | 6                                               |
| Max. voltage drop switching output AC           | [V]  | 6.5                                             |
| Minimum load current                            | [mA] | 5                                               |
| Max. leakage current                            | [mA] | 2.5 (250 V AC) / 1.3 (110 V AC) / 0.8 (24 V DC) |
| Permanent current rating of switching output AC | [mA] | 250; (350 (...50 °C))                           |
| Permanent current rating of switching output DC | [mA] | 100                                             |
| Short-time current rating of switching output   | [mA] | 2200; (20 ms / 0,5 Hz)                          |
| Switching frequency AC                          | [Hz] | 25                                              |
| Switching frequency DC                          | [Hz] | 50                                              |
| Short-circuit proof                             |      | no                                              |
| Overload protection                             |      | no                                              |

### Detection zone


|                       |      |          |
|-----------------------|------|----------|
| Sensing range         | [mm] | 8        |
| Real sensing range Sr | [mm] | 8 ± 10 % |
| Operating distance    | [mm] | 0...6.5  |



## Inductive sensor

IGA2008-BBOA/20m

| Accuracy / deviations         |                                                                               |                  |
|-------------------------------|-------------------------------------------------------------------------------|------------------|
| Correction factor             | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2   |                  |
| Hysteresis                    | [% of Sr]                                                                     | 1...15           |
| Switch point drift            | [% of Sr]                                                                     | -10...10         |
| Operating conditions          |                                                                               |                  |
| Ambient temperature           | [°C]                                                                          | -25...80         |
| Protection                    | IP 67                                                                         |                  |
| Tests / approvals             |                                                                               |                  |
| EMC                           | EN 60947-5-2                                                                  |                  |
|                               | EN 55011                                                                      | class B          |
| MTTF                          | [years]                                                                       | 604              |
| Mechanical data               |                                                                               |                  |
| Housing                       | threaded type                                                                 |                  |
| Mounting                      | non-flush mountable                                                           |                  |
| Dimensions                    | [mm]                                                                          | M18 x 1 / L = 80 |
| Thread designation            | M18 x 1                                                                       |                  |
| Materials                     | housing: brass white bronze coated; sensing face: PBT                         |                  |
| Displays / operating elements |                                                                               |                  |
| Display                       | switching status                                                              | 1 x LED, yellow  |
| Electrical connection         |                                                                               |                  |
| Required protection           | miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting                      |                  |
| Accessories                   |                                                                               |                  |
| Items supplied                | lock nuts: 2                                                                  |                  |
| Remarks                       |                                                                               |                  |
| Remarks                       | Recommendation: Check the safe functioning of the unit after a short circuit. |                  |
| Pack quantity                 | 1 pcs.                                                                        |                  |
| Electrical connection         |                                                                               |                  |
| Cable: 20 m, PVC; 2 x 0.5 mm² |                                                                               |                  |
| Connection                    |                                                                               |                  |



Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting

Core colours :

BN = brown  
BU = blue