


Inductive sensor

SIH-3010-ANKG

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	10
Housing	threaded type
Dimensions [mm]	M22 x 1

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs


Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	250
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes



Inductive sensor

SIH-3010-ANKG

Detection zone		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	$10 \pm 10 \%$
Operating distance	[mm]	0...8.1
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M22 x 1
Thread designation		M22 x 1
Materials		brass white bronze coated; PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.5 mm ²		
Connection		



Core colours :

BN = brown

BU = blue

BK = black