


Inductive sensor

IF-2002-BBOW/ 6m

Article no longer available - archive entry



Product characteristics

Output function		normally closed
Sensing range	[mm]	2
Housing		threaded type
Dimensions	[mm]	M12 x 1 / L = 71.5

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC
Protection class		II
Reverse polarity protection		no

Outputs

Output function		normally closed
Max. voltage drop switching output AC	[V]	8.5
Minimum load current	[mA]	8
Max. leakage current	[mA]	2
Permanent current rating of switching output AC	[mA]	200; (250 (...50 °C))
Short-time current rating of switching output	[mA]	900; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Short-circuit proof		no
Overload protection		no

Detection zone

Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
---------------------	------	----------

**Inductive sensor**

IF-2002-BBOW/ 6m

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	932

Mechanical data

Housing	threaded type
Mounting	flush mountable
Dimensions [mm]	M12 x 1 / L = 71.5
Thread designation	M12 x 1
Materials	PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Electrical connection


Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting
---------------------	---

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Remarks	Recommendation: Check the safe functioning of the unit after a short circuit.
Pack quantity	1 pcs.

Electrical connectionCable: 6 m, PVC; 2 x 0.5 mm²**Connection**Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting

Core colours :

BN =

brown

BU =

blue