


Diffuse reflection sensor

OUN-DPKG/US-100-DPO

Article no longer available - archive entry



receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Special feature	Diffuse reflection sensor for short ranges
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	< 35
Protection class		III
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	20...40; (white paper 200 x 200 mm)
Max. light spot diameter	[mm]	20
Light spot dimensions refer to		at maximum range
Diffuse reflection sensor for short ranges		yes



Diffuse reflection sensor


OUN-DPKG/US-100-DPO

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Weight	[g]	70.6
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Materials		PPO modified
Lens material		glass
Lens alignment		side lens
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied	Angle bracket: 1, E20211	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		

Connector: 1 x M12; coding: A



Connection





Diffuse reflection sensor

OUN-DPKG/US-100-DPO

Diagrams and graphs

excess gain graph

