

IM5027




Inductive sensor

IME3015-FNKG

Article no longer available - archive entry

Alternative articles: IM5038
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		NPN
Output function		normally open / normally closed; (selectable)
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 120
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		NPN
Output function		normally open / normally closed; (selectable)



Inductive sensor

IME3015-FNKG

Max. voltage drop switching output DC	[V]	1.6	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	350	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Sensing range	[mm]	15	
Real sensing range Sr	[mm]	15 ± 10 %	
Operating distance	[mm]	0...12.1	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 65	
Tests / approvals			
EMC	EN 60947-5-2		
Mechanical data			
Housing		rectangular	
Mounting		flush mountable	
Dimensions	[mm]	40 x 40 x 120	
Materials		PPE modified	
Displays / operating elements			
Display	switching status		1 x LED, yellow
Remarks			
Remarks	5 positions of the active zone possible		
Pack quantity	1 pcs.		

IM5027



Inductive sensor

IME3015-FNKG

Electrical connection

terminals: ...2.5 mm²; Cable sheath: Ø 7...13 mm

Connection

