


Flow transmitter with integrated backflow prevention

SBG34HF010KG/US

Please note the changed housing design!

**Product characteristics**

Measuring range	[l/min]	4...100
Process connection		threaded connection G 3/4

Application

Media	Liquids; water; glycol solutions; coolants	
Medium temperature	[°C]	-10...100
Pressure rating	[bar]	25
Pressure rating	[MPa]	2.5

Electrical data

Operating voltage	[V]	18...32 DC; (to SELV/PELV)
Current consumption	[mA]	< 35
Protection class		III

SBG446



Flow transmitter with integrated backflow prevention

SBG34HF010KG/US

Reverse polarity protection		yes
Outputs		
Output signal		analogue signal
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Overload protection		yes
Measuring/setting range		
Measuring range	[l/min]	4...100
Accuracy / deviations		
Repeatability [% of the final value]		1
Measuring error [% of the final value]		± 5
Response times		
Response time	[s]	< 0.01
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-15...80
Protection		IP 65; IP 67
Tests / approvals		
EMC		DIN EN 61000-6-2
		DIN EN 61000-6-3
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-6
MTTF	[years]	778
Mechanical data		
Weight	[g]	1297.6
Materials		brass chemically nickel-plated; PP; stainless steel (316L/1.4404); aluminium anodised; PA
Materials (wetted parts)		stainless steel (316 / 1.4401); brass; brass chemically nickel-plated; PP; PPS; O-ring: FKM
Process connection		threaded connection G 3/4
Switching cycles mechanical		10 million
Remarks		
Remarks		Recommendation Use 200 micron filtration All data refer to water (20 °C).
Notes		Please note the changed housing design!
Pack quantity		1 pcs.

SBG446



Flow transmitter with integrated backflow prevention


SBG34HF010KG/US

Electrical connection

Connector: 1 x M12; coding: A



Connection




colours to DIN EN 60947-5-2

Core colours :

BN =	brown
BU =	blue
WH =	white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity