




AS-Interface CANopen gateway with PLC

ControllerE 1Mstr CO RS232

Article no longer available - archive entry

Alternative articles: AC1331
When selecting an alternative article and accessories please note that technical data may differ!



Application	
Application	decentralised controller; CANopen gateway
Electrical data	
Operating voltage [V]	24 DC; ("supply class 2" to cULus)
Current consumption [mA]	< 500
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Number of AS-i masters	1
Interfaces	
Communication interface	RS232; CAN
CAN	
Number of CAN interfaces	1



AS-Interface CANopen gateway with PLC

ControllerE 1Mstr CO RS232

Protocol		CANopen	
Usage type		data transmission	
RS232			
Number of R232 interfaces		1	
Transmission rate		9600...115200 Baud	
Connector type		RJ11	
Usage type		programming	
Note on interfaces		electrically isolated	
Operating conditions			
Ambient temperature	[°C]	0...60	
Storage temperature	[°C]	-20...70	
Max. relative air humidity	[%]	95	
Protection		IP 20	
AS-i classification			
AS-i version		2.1	
AS-i master profile		M3	
AS-i certificate		61107	
Mechanical data			
Housing		housing for DIN rail mounting	
Materials		aluminium; steel sheet galvanised	
Displays / operating elements			
Display	function	3 x LED, red	
		2 x LED, green	
		2 x LED, yellow	
		full graphic LCD display	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Connection			

