


ANT515



RFID read/write head HF

DTRHF KQRWIDUS03-



- | | |
|---|--------------|
| 1 | LED |
| 2 | Sensing face |



Application

Application	detection of objects on transport equipment
Radio approval for	USA; Canada; EU/RED; Australia; Japan; China; Taiwan; India; Singapore; Ukraine; Malaysia
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under “Downloads”.

Electrical data

Operating voltage	[V]	19.2...28.8 DC; (supply only via the DTE10x evaluation unit (to EN 60950-1))
Current consumption	[mA]	< 50
Protection class		III
Operating frequency	[MHz]	13,56
RFID standard		ISO 15693

Detection zone

Distance write/read head front	[mm]	120		
Distance write/read head side	[mm]	100		
Distance to the ID tag	[mm]	referred to 30 mm coin tag and antenna installed on metal, I-CODE SLI	:	≤ 32

Interfaces

Communication interface	DATA / DTE10x
-------------------------	---------------

Operating conditions

Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Protection		IP 67; IP 69K

Tests / approvals

EMC	DIN EN 61000-6-2	
Shock resistance	EN 60068-2-27	50 g 11 ms / 40 g (6 ms, continuous)
Vibration resistance	EN 60068-2-6	20 g 10...2000 Hz
Radio approval	EN 302 291-1 V1.1.1 / EN 302 291-2 V1.1.1	



RFID read/write head HF

DTRHF KQRWIDUS03-

MTTF	[years]	457.9
------	---------	-------

Mechanical data

Weight	[g]	80
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	20 x 7 x 48
Materials		PBT; TPE-U; stainless steel

Displays / operating elements

Display	operation	1 x LED, green
	tag communication	1 x LED, yellow

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 1 m, PUR; 3 x 0.14 mm²

Connector: 1 x M12; coding: A



Connection

