


OM5005

Fibre-optic amplifier

OMF-FCKG/US-100



receiver in lower lens
transmitter in upper lens



Product characteristics

Type of light	red light
Housing	rectangular

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 80
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660
Typ. lifetime	[h]	100000
Reference temperature for service life	[°C]	25

Outputs

Electrical design	PNP/NPN	
Output function	light-on/dark-on mode; (programmable)	
Max. voltage drop switching output DC	[V]	2
Max. voltage drop of function check output	[V]	2
Max. current load for function check output	[mA]	100
Permanent current rating of switching output DC	[mA]	100

OM5005



Fibre-optic amplifier

OMF-FCKG/US-100

Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[m]	< 0.8; (Through-beam sensor)
Range	[mm]	< 175; (in diffuse reflection mode)
Range adjustable		yes

Response times

Response time	[s]	< 1
---------------	-----	-----

Operating conditions

Ambient temperature	[°C]	-25...40
Protection		IP 67

Tests / approvals

EMC	IEC 1000-4-2/3/4/5/6	
-----	----------------------	--

Mechanical data

Weight	[g]	199
Housing		rectangular
Dimensions	[mm]	73 x 45 x 49
Materials		ABS glass fibre reinforced
Lens material		PMMA
Lens alignment		side lens

Displays / operating elements


Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Locking: aluminium, uncoloured anodised




OM5005

Fibre-optic amplifier

OMF-FCKG/US-100



Connection



5

Function check output