


# PN7320



## Pressure sensor with display

PN-600PSBU76-QFPKG/US/ IV

Article no longer available - archive entry



- 1 7-segment LED display  
2 programming button



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2
Measuring range [psi]	0...6000
Process connection	threaded connection 7/16" - 20 UNF internal thread

### Application

Special feature	Gold-plated contacts
Application	for industrial applications
Media	liquids and gases
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.
Medium temperature [°C]	-25...80
Min. bursting pressure [psi]	14000
Pressure rating [psi]	8500
Type of pressure	relative pressure

### Electrical data

Operating voltage [V]	18...30 DC
Current consumption [mA]	< 60
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	0.2

# PN7320



## Pressure sensor with display

PN-600PSBU76-QFPKG/US/ IV

Integrated watchdog	yes									
<b>Inputs / outputs</b>										
Number of inputs and outputs	Number of digital outputs: 2									
<b>Outputs</b>										
Total number of outputs	2									
Output signal	switching signal									
Electrical design	PNP									
Number of digital outputs	2									
Output function	normally open / normally closed; (parameterisable)									
Max. voltage drop switching output DC [V]	2									
Permanent current rating of switching output DC [mA]	250									
Short-circuit protection	yes									
Type of short-circuit protection	pulsed									
Overload protection	yes									
<b>Measuring/setting range</b>										
Measuring range [psi]	0...6000									
Set point SP [psi]	60...6000									
Reset point rP [psi]	30...5970									
In steps of [psi]	30									
<b>Accuracy / deviations</b>										
Switch point accuracy [% of the final value]	< ± 1,0									
Repeatability [% of the final value]	< ± 0,25; (with temperature fluctuations < 10 K)									
Characteristics deviation [% of the final value]	< ± 0,25 (BFSL) / < ± 0,5 (LS)									
Temperature drift per 10 K	< ± 0.3									
<b>Response times</b>										
Switching frequency for a given set response time of one output	Response time [ms] (dAP)	3	6	10	17	30	60	125	250	500
	Switching frequency [Hz]	170	80	50	30	16	8	4	2	1
Response time [ms]	at rectangular pressure characteristic; switch point (SPx) = 70 %; reset point (rPx) = 30 %									
Delay time programmable dS, dr [s]	0, 0,2,...10, 11,...50									
<b>Software / programming</b>										
Adjustment of the switch point	programming button									
Parameter setting options	hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping									
<b>Operating conditions</b>										
Ambient temperature [°C]	-25...80									
Storage temperature [°C]	-40...100									

# PN7320



## Pressure sensor with display

PN-600PSBU76-QFPKG/US/ IV

Protection	IP 67
------------	-------

### Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

### Mechanical data

Materials	EPDM/X; FKM; PA; PBT; PC; stainless steel (304/1.4301)
Materials (wetted parts)	stainless steel (303/1.4305); ceramics; FKM
Min. pressure cycles	100 million
Process connection	threaded connection 7/16" - 20 UNF internal thread

### Displays / operating elements

Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection

