


# IF5126



## Inductive sensor

IFK3004-BPOG/V4A/ 6m

Article no longer available - archive entry



### Product characteristics

|                    |               |
|--------------------|---------------|
| Electrical design  | PNP           |
| Output function    | normally open |
| Sensing range [mm] | 4             |
| Housing            | threaded type |
| Dimensions [mm]    | M12 x 1       |

### Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...30 DC |
| Current consumption [mA]    | 15; (24 V) |
| Protection class            | II         |
| Reverse polarity protection | no         |

### Outputs

|                                                      |               |
|------------------------------------------------------|---------------|
| Electrical design                                    | PNP           |
| Output function                                      | normally open |
| Max. voltage drop switching output DC [V]            | 1             |
| Permanent current rating of switching output DC [mA] | 200           |
| Switching frequency DC [Hz]                          | 300           |
| Short-circuit protection                             | no            |
| Overload protection                                  | no            |

### Detection zone

|                            |          |
|----------------------------|----------|
| Sensing range [mm]         | 4        |
| Real sensing range Sr [mm] | 4 ± 10 % |
| Operating distance [mm]    | 0...3.25 |

### Accuracy / deviations

|                              |                                                                             |
|------------------------------|-----------------------------------------------------------------------------|
| Correction factor            | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |
| Hysteresis [% of Sr]         | 1...15                                                                      |
| Switch point drift [% of Sr] | -10...10                                                                    |

### Operating conditions

|                          |          |
|--------------------------|----------|
| Ambient temperature [°C] | -25...80 |
|--------------------------|----------|

# IF5126



## Inductive sensor

IFK3004-BPOG/V4A/ 6m

|            |       |
|------------|-------|
| Protection | IP 67 |
|------------|-------|

### Tests / approvals

|     |              |         |
|-----|--------------|---------|
| EMC | EN 60947-5-2 |         |
|     | EN 55011     | class B |

### Mechanical data

|                    |                                     |
|--------------------|-------------------------------------|
| Housing            | threaded type                       |
| Mounting           | non-flush mountable                 |
| Dimensions [mm]    | M12 x 1                             |
| Thread designation | M12 x 1                             |
| Materials          | stainless steel (316Ti/1.4571); PBT |

### Accessories

|                |              |
|----------------|--------------|
| Items supplied | lock nuts: 2 |
|----------------|--------------|


### Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

### Electrical connection

Cable: 6 m, PVC; 3 x 0.34 mm<sup>2</sup>

#### Connection



|      |                |
|------|----------------|
|      | Core colours : |
| BN = | brown          |
| BU = | blue           |
| BK = | black          |