


## Pressure sensor with display

PI-150-REA01-MFRKG/US/ /P

Article no longer available - archive entry

Alternative articles: PL1512

When selecting an alternative article and accessories please note that technical data may differ!



- 1 alphanumeric display 4-digit  
 2 status LEDs  
 3 programming button

EHEDG Tested

## Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1
Measuring range [bar]	-1...150
Process connection	threaded connection G 1 external thread sealing cone
<b>Application</b>	
Special feature	Gold-plated contacts
Installation	freely rotatable housing 350°
Media	liquids and gases
Conditionally suitable for	use in gases at pressures > 25 bar only on request
Medium temperature [°C]	-25...125; (145 max. 1h)
Min. bursting pressure [bar]	650
Pressure rating [bar]	200
Type of pressure	relative pressure; vacuum

# PY2692



## Pressure sensor with display

PI-150-REA01-MFRKG/US/ IP

No dead space		yes
<b>Electrical data</b>		
Operating voltage	[V]	18...32 DC
Current consumption	[mA]	< 50
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.5
Integrated watchdog		yes
<b>Inputs / outputs</b>		
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1
<b>Outputs</b>		
Total number of outputs		2
Output signal		switching signal; analogue signal; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	6
Number of analogue outputs		1
Analogue current output	[mA]	4...20, invertible; (scalable 1:4)
Max. load	[Ω]	(Ub - 10 V) / 20 mA
Analogue voltage output	[V]	0...10, invertible; (scalable 1:4)
Min. load resistance	[Ω]	2000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
<b>Measuring/setting range</b>		
Measuring range	[bar]	-1...150
Set point SP	[bar]	-0.8...150
Reset point rP	[bar]	-1...149.8
Analogue start point	[bar]	-1...112.5
Analogue end point	[bar]	36.5...150
In steps of	[bar]	0.1
<b>Accuracy / deviations</b>		
Switch point accuracy	[% of the span]	< ± 0,5; (Turn down 1:1)
Repeatability	[% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation	[% of the span]	< ± 0,5; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)
Linearity deviation		< ± 0,15; (Turn down 1:1)

**Pressure sensor with display**

PI-150-REA01-MFRKG/US/ /P

[% of the span]		
Hysteresis deviation [% of the span]		< ± 0,15; (Turn down 1:1)
Long-term stability [% of the span]		< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point [% of the span / 10 K]		< ± 0,05; (0...70 °C)
Temperature coefficient span [% of the span / 10 K]		< ± 0,15; (0...70 °C)
Response times		
Response time [ms]		< 100
Damping process value dAP [s]		0.1...100
Damping for the analogue output dAA [s]		0.1...100
Max. response time analogue output [ms]		100
Software / programming		
Parameter setting options		hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span
Operating conditions		
Ambient temperature [°C]		-25...80
Storage temperature [°C]		-40...100
Protection		IP 67; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD EN 61000-4-3 HF radiated EN 61000-4-4 Burst EN 61000-4-5 Surge EN 61000-4-6 HF conducted	4 kV CD / 8 kV AD 10 V/m 2 kV 0,5/1 kV 10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight [g]		450
Materials	stainless steel (316L/1.4404); PC; PBT; PEI; FKM; PTFE	
Materials (wetted parts)	stainless steel (316L/1.4435); ceramics; PTFE	
Min. pressure cycles	100 million	
Process connection	threaded connection G 1 external thread sealing cone	
Displays / operating elements		
Display	Display unit switching status function display measured values	4 x LED, green LED, yellow alphanumeric display, 4-digit alphanumeric display, 4-digit
Display unit	bar; psi; MPa; % of the span	

## Pressure sensor with display

PI-150-REA01-MFRKG/US /P


### Remarks

Pack quantity



1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



OUT1  
OUT2

switching output  
analogue output