




Control monitor for flow sensors

VS0200/230VAC

Article no longer available - archive entry

Alternative articles: SN0150
When selecting an alternative article and accessories please note that technical data may differ!




Application		
Application	Flow monitoring; Wire monitoring	
Electrical data		
Operating voltage tolerance	[%]	-10...10
Operating voltage	[V]	< 230 AC
Max. power consumption	[VA]	3
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design	relay	
Contact rating	4 A, 250 V AC	
Switching function flow monitoring	relay energised when flow is present	
Switching function wire break monitoring	relay de-energised in case of wire break and short circuit	
Response times		
Response time	[s]	< 10
Software / programming		
Adjustment of the switch point	potentiometer	
Selection liquids / gases	slide switch	



Control monitor for flow sensors

VS0200/230VAC

Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 40
Protection rating terminals		IP 20
Mechanical data		
Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110
Materials		plastics
Displays / operating elements		
Display	function	11 x LED
	switching status	LED, red
Remarks		
Pack quantity		1 pcs.
Electrical connection		
terminals: 16 x ...2.5 mm ²		
Connection		



- 1: Relais Wire monitoring
 2: Relais Flow monitoring
 Core colours :
 BN = brown
 BU = blue
 BK = black
 WH = white
 GY = grey