

SR0100




Control monitor for flow sensors

VS0200/ 24VDC

Article no longer available - archive entry

Alternative articles: SR0150
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application	Flow monitoring	
Electrical data		
Operating voltage tolerance	[%]	-10...10
Operating voltage	[V]	24 DC
Current consumption	[mA]	60
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design	relay	
Contact rating	4 A, 250 V AC	
Switching function flow monitoring	relay energised when flow is present	
Software / programming		
Adjustment of the switch point	potentiometer	
Selection liquids / gases	slide switch	
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 40
Protection rating terminals		IP 20

SR0100



Control monitor for flow sensors

VS0200/ 24VDC

Mechanical data		
Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110
Materials		plastics


Displays / operating elements		
Display	function	11 x LED

Remarks		
Pack quantity		1 pcs.

Electrical connection

terminals: 16 x ...2.5 mm²

Connection



- 1: Relais Flow monitoring
Core colours :
- BN = brown
BU = blue
BK = black
WH = white
GY = grey