




Pushbutton module with knob with push and joystick function in two axes and with backlit keys

ecomatPanel/COP



- 1 pushbuttons
- 2 knob



Product characteristics

Communication interface	CAN
Dimensions [mm]	136 x 86 x 73.5

Application

Design	installation in panels or panel cutouts
--------	---

Electrical data

Operating voltage [V]	9...32 DC
Nominal voltage DC [V]	12 / 24
Current consumption [mA]	< 400; (13,5 V DC)
Reverse polarity protection	yes



Pushbutton module with knob with push and joystick function in two axes and with backlit keys

ecomatPanel/COP

Interfaces		
Communication interface		CAN
Number of CAN interfaces		1
CAN		
Protocol		J1939
Factory settings		Baud rate: 250
		node ID: 135
Note on interfaces		dynamic address allocation is supported
Operating conditions		
Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...85
Max. relative air humidity	[%]	90
Max. height above sea level	[m]	4000
Protection		IP 65
Tests / approvals		
EMC	UN/ECE-R10 noise emission and noise immunity:	100 V/m
	DIN EN 61000-6-2 ESD	
	DIN EN 61000-6-4 Burst	
	ISO 7637-2 pulse 1	severity level 4 / function state C (24 V)
	ISO 7637-2 pulse 2a	severity level 4 / function state A (24 V)
	ISO 7637-2 pulse 2b	severity level 4 / function state C (24 V)
	ISO 7637-2 pulse 3a	severity level 4 / function state A (24 V)
	ISO 7637-2 pulse 3b	severity level 4 / function state A (24 V)
	ISO 7637-2 pulse 4	severity level 4 / function state B (24 V)
	ISO 7637-2 pulse 5b	severity level 4 / function state A (24 V)
ISO 7637-2 pulse 4	severity level 4 / function state B (12 V)	
Continuous shock resistance	ISO 16750-3	30 g 6 ms / 24000 shocks
Fast temperature change	EN 60068-2-30 damp heat: cyclical	55 ° C upper temperature limit / 6 cycles
	EN 60068-2-78 damp heat: constant	40 ° C 93 % rH / test period 21 days
Vibration resistance	ISO 16750-3 Test VII	random, mounting place car body
	EN 60068-2-6 Sinus	10...500 Hz / 10 cycles/axis, sine
Salt spray test	EN 60068-2-52 Salt spray	severity level 3 / motor vehicle
MTTF	[years]	119
Mechanical data		
Weight	[g]	459.6
Weight (without accessories and packaging)	[g]	400
Dimensions	[mm]	136 x 86 x 73.5
Materials		housing: PC/ABS; silicone overlay: PA66 transparent
Information on service life	pushbuttons:	> 100000 activations
	knob (rotation by 360°):	> 100000 cycles
	knob (push function):	> 100000 activations
	knob (tilting per axis):	> 100000 activations
Displays / operating elements		
Display		LED, multi-colour

CR1300



Pushbutton module with knob with push and joystick
function in two axes and with backlit keys


ecomatPanel/COP

Operating elements	6	freely programmable backlit function keys
	1	\$Drehknopf_mit_Tast_und_Joystick_Funktion_in_zwe
		24 stops per revolution

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection



1	CAN_L
2	CAN_H
3	GNB
4	VBB