


LMT04A



Sensor for point level detection in hazardous areas

LMECE-A12E-QSKG-1/US/3D/3G



1 Tightening torque 20...25 Nm



EC 1935/2004 EHEDG Tested



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2
Factory setting	oils; oil-based media; powder
Process connection	threaded connection G 1/2 sealing cone

Application

Special feature	Gold-plated contacts
Media	Liquids; viscous media; powder
Cannot be used for	See the operating instructions, chapter "Function and features".
Medium temperature [°C]	-20...85
Probe length [mm]	253
Tank pressure [bar]	-1...40

Electrical data

Operating voltage [V]	18...30 DC
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes
Measuring principle	capacitive

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

Outputs

Total number of outputs	2
Output signal	switching signal; IO-Link
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2.5

LMT04A



Sensor for point level detection in hazardous areas

LMECE-A12E-QSKG-1/US/3D/3G

Permanent current rating of switching output DC [mA]	100
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Factory setting	oils; oil-based media; powder
-----------------	-------------------------------

Response times

Response time [s]	< 0.5
-------------------	-------

Interfaces

Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
SDCI standard	IEC 61131-9				
Profiles	Smart Sensor: Process Data Variable; Device Identification				
SIO mode	yes				
Required master port type	A				
Process data analogue	1				
Process data binary	2				
Min. process cycle time [ms]	2.3				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>642</td></tr> </table>	Type of operation	DeviceID	default	642
Type of operation	DeviceID				
default	642				

Operating conditions

Ambient temperature [°C]	-20...60
Storage temperature [°C]	-40...85
Protection	IP 67; (when used outside the hazardous area: IP 68 / IP 69)

Tests / approvals

ATEX marking	Ex II 3D Ex tc IIIC T90°C Dc X
	Ex II 3G Ex nA IIC T4 Gc X
EMC	DIN EN 61000-6-2
	DIN EN 61000-6-4 closed tanks
Shock resistance	DIN EN 60068-2-27 50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6 8 g (10...2000 Hz)
MTTF [years]	223

Mechanical data

Weight [g]	362
Materials	stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEEK; PEI; FKM
Materials (wetted parts)	stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEEK; surface characteristics: Ra < 0,8 / Rz 4; FKM
Process connection	threaded connection G 1/2 sealing cone

Displays / operating elements

Display	switching status	LED, yellow
	operating status	LED, green

LMT04A



Sensor for point level detection in hazardous areas

LMECE-A12E-QSKG-1/US/3D/3G

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1: switching output IO-Link Teach
OUT2: switching output
colours to DIN EN 60947-5-2
Core colours :
BK = black
BN = brown
BU = blue
WH = white