




Cylinder sensor for tie-rod cylinder

MKZ3000-BPKG/US-100-DPS

Article no longer available - archive entry



1 Sensing face



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	30 x 30 x 23

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Reverse polarity protection	yes
Max. power-on delay time [ms]	2

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	300
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Response sensitivity [mT]	2
---------------------------	---

MK5048



Cylinder sensor for tie-rod cylinder

MKZ3000-BPKG/US-100-DPS

Travel speed	[m/s]	< 5
--------------	-------	-----

Accuracy / deviations

Hysteresis	[mm]	1
Repeatability	[mm]	0.1

Operating conditions

Ambient temperature	[°C]	-25...75
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)

Mechanical data

Sensing face		front
Cylinder type		tie rod cylinders; (Joucomatic)
Dimensions	[mm]	30 x 30 x 23
Materials		aluminium; plastics

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection

