


## Through-beam sensor transmitter

OGS-00KG/V4A/US-100

Article no longer available - archive entry

Alternative articles: OGS300

When selecting an alternative article and accessories please note that technical data may differ!



## Product characteristics

Type of light	infrared light
Housing	threaded type

## Application

Special feature	Gold-plated contacts
Function principle	Through-beam sensor

## Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 17
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

## Outputs

Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

## Detection zone

Transmitter / receiver	transmitter
Range [m]	< 15
Range adjustable	no
Max. light spot diameter [mm]	2000
Light spot dimensions refer to	at maximum range

## Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 68; IP 69K



## Through-beam sensor transmitter

OGS-OOKG/V4A/US-100

## Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

## Mechanical data

Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 60.5
Thread designation	M18 x 1
Materials	stainless steel (316L/1.4404); PBT
Lens material	PMMA

## Displays / operating elements

Display	operation	1 x LED, green
---------	-----------	----------------

## Accessories

Items supplied	lock nuts: 2
----------------	--------------

## Remarks

Pack quantity	1 pcs.
---------------	--------

## Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



## Connection

