


Infrared temperature sensor

OWF-9000-BPKG

Article no longer available - archive entry

Alternative articles: TW7011 + E35061 + E35065

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Housing	cylindrical
---------	-------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	< 20
Protection class		II
Reverse polarity protection		yes

Outputs

Electrical design		PNP
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes



Infrared temperature sensor

OWF-9000-BPKG

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Detection range hysteresis [%]	1...15
--------------------------------	--------

Operating conditions

Ambient temperature [°C]	-20...60
Protection	IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	cylindrical
Dimensions [mm]	Ø 58 / L = 129
Materials	housing: brass white bronze coated
Lens material	glass

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	Fibre optics with aluminium sheathing
----------------	---------------------------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x 7/8"



Connection

