PE3021


Pressure sensor with display

PE-250-SBR14-KFPKG/US/ /E

Article no longer available - archive entry

Alternative articles: PE3001

When selecting an alternative article and accessories please note that technical data may differ!



1 7-segment LED display
2 programming button

Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1
Measuring range	[bar]	0...250
Process connection		threaded connection G 1/4 internal thread
Application		
Special feature		Gold-plated contacts
Application		for industrial applications
Media		liquids and gases
Conditionally suitable for		For gaseous media the application is limited to max. 25 bar.
Cannot be used for		oils
Medium temperature	[°C]	-25...80
Min. bursting pressure	[bar]	850
Pressure rating	[bar]	400
Type of pressure		relative pressure
Electrical data		
Operating voltage	[V]	20...30 DC
Current consumption	[mA]	< 60

PE3021

Pressure sensor with display

PE-250-SBR14-KFPKG/US/ /E

Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.2
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; (configurable)
Electrical design		PNP
Number of digital outputs		1
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range	[bar]	0...250
Set point SP	[bar]	2...250
Reset point rP	[bar]	1...248
In steps of	[bar]	1
Accuracy / deviations		
Switch point accuracy [% of the final value]		< ± 1,5
Repeatability [% of the final value]		< ± 0,25; (with temperature fluctuations < 10 K)
Characteristics deviation [% of the final value]		< ± 1,0
Temperature drift per 10 K		< ± 0.3
Response times		
Switching frequency for a given set response time of one output		

Response time (dAP) [ms]	3	6	10	17	30	60	125	250	500
Switching frequency [Hz]	170	80	50	30	16	8	4	2	1

Response time	[ms]	at rectangular pressure characteristic; switch point (SPx) = 70 %; reset point (rPx) = 30 %
Delay time programmable dS, dr	[s]	0, 0,2,...10, 11,...50
Max. response time analogue output	[ms]	3

PE3021

Pressure sensor with display

PE-250-SBR14-KFPKG/US/ /E

Software / programming			
Adjustment of the switch point		programming button	
Parameter setting options		hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data			
Materials		EPDM/X; FKM; PA; PBT; PC; stainless steel (1.4301 / 304)	
Materials (wetted parts)		EPDM/X; ceramics; stainless steel (1.4305 / 303)	
Min. pressure cycles		100 million	
Process connection		threaded connection G 1/4 internal thread	
Displays / operating elements			
Display		switching status	LED, red
		function display	7-segment LED display
		measured values	7-segment LED display
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Connector: 1 x M12; coding: A; Contacts: gold-plated



PE3021

Pressure sensor with display

PE-250-SBR14-KFPKG/US/ /E

Connection

