


Flow sensor with integrated backflow prevention

SBY32BF0BPKG/US



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Process connection	Rp 1 1/2

Application

Media	Liquids; water; glycol solutions; coolants
Medium temperature [°C]	0...85
Pressure rating [bar]	25
Pressure rating [MPa]	2.5

Electrical data

Operating voltage [V]	10...30 DC; (to SELV/PELV)
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Outputs

Total number of outputs	1
Output signal	switching signal
Electrical design	PNP

SBY357



Flow sensor with integrated backflow prevention

SBY32BF0BPKG/US

Number of digital outputs	1
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Short-circuit protection	yes
Overload protection	yes
Measuring/setting range	
Setting range [l/min]	20...200
Accuracy / deviations	
Repeatability [% of the final value]	1
Hysteresis [l/min]	5...10
Measuring error [% of the final value]	± 5
Response times	
Response time [s]	< 0.01
Operating conditions	
Ambient temperature [°C]	0...60
Storage temperature [°C]	-15...80
Protection	IP 65; IP 67
Tests / approvals	
EMC	DIN EN 61000-6-2
	DIN EN 61000-6-3
Shock resistance	DIN EN 60068-2-27
Vibration resistance	DIN EN 60068-2-6
MTTF [years]	3318
Mechanical data	
Weight [g]	2141.8
Materials	brass chemically nickel-plated; PP; aluminium anodised; PA
Materials (wetted parts)	stainless steel (301/1.4310); stainless steel (304/1.4301); PBT; brass chemically nickel-plated; PP; PPS; Polyolefin; O-ring: FKM
Process connection	Rp 1 1/2
Switching cycles mechanical	10 million
Displays / operating elements	
Display	switching status
	4 x LED, yellow
Accessories	
Items supplied	Allen key
Remarks	
Remarks	Caution Do not turn the cap beyond the maximum value of the setting range.
	All data refer to water (20 °C).
Pack quantity	1 pcs.

Flow sensor with integrated backflow prevention


SBY32BF0BPKG/US

Electrical connection

Connector: 1 x M12; coding: A




Connection



Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity