
# IGT247

## Inductive full-metal sensor

IGK3005-BPKG/AM/US-104




EC 1935/2004

| | | |
|---|---|---|
| **Product characteristics** | | |
| Electrical design | | PNP |
| Output function | | normally open |
| Sensing range | [mm] | 5 |
| Housing | | threaded type |
| Dimensions | [mm] | M18 x 1 / L = 70 |
| **Application** | | |
| Special feature | | Gold-plated contacts; Full-metal housing |
| Application | | Use in wet areas and in the food and beverage industry |
| Pressure rating | [bar] | 100 |
| Note on pressure rating | | sensing face |
| **Electrical data** | | |
| Operating voltage | [V] | 10...36 DC |
| Current consumption | [mA] | < 20 |
| Protection class | | III |
| Reverse polarity protection | | yes |
| **Outputs** | | |
| Electrical design | | PNP |
| Output function | | normally open |
| Max. voltage drop switching output DC | [V] | 2.5 |
| Permanent current rating of switching output DC | [mA] | 100 |
| Switching frequency DC | [Hz] | 100 |
| Short-circuit protection | | yes |
| Type of short-circuit protection | | pulsed |
| Overload protection | | yes |
| **Detection zone** | | |
| Sensing range | [mm] | 5 |
| Operating distance | [mm] | 0...4.05 |

# IGT247


## Inductive full-metal sensor

IGK3005-BPKG/AM/US-104

| | | | |
|---|---|---|---|
| **Accuracy / deviations** | | | |
| Correction factor | | steel: 1 / stainless steel: 0.7 / brass: 0.6 / aluminium: 0.5 / copper: 0.3 | |
| Hysteresis | [% of Sr] | 1...20 | |
| **Operating conditions** | | | |
| Ambient temperature | [°C] | 0...100 | |
| Protection | | IP 68; IP 69K | |
| **Tests / approvals** | | | |
| EMC | | EN 61000-4-2 ESD | 4 kV CD / 8 kV AD |
| | | EN 61000-4-3 HF radiated | 10 V/m |
| | | EN 61000-4-4 Burst | 2 kV |
| | | EN 61000-4-6 HF conducted | 10 V |
| | | EN 55011 emission | class B |
| Impact resistance | | | 1 J |
| MTTF | [years] | 1258 | |
| UL approval | | Ta | -25...70 °C |
| | | Enclosure type | Type 1 |
| | | power supply | Limited Voltage/Current |
| | | UL Approval no. | A012 |
| | | File number UL | E174191 |
| **Mechanical data** | | | |
| Weight | [g] | 55 | |
| Housing | | threaded type | |
| Mounting | | flush mountable | |
| Dimensions | [mm] | M18 x 1 / L = 70 | |
| Thread designation | | M18 x 1 | |
| Materials | | housing: stainless steel (1.4404 / 316L); sensing face: stainless steel (1.4404 / 316L); lock nuts: stainless steel (1.4404 / 316L) | |
| Full-metal housing | | yes | |
| **Displays / operating elements** | | | |
| Display | | switching status | 4 x 90° LED, yellow |
| **Accessories** | | | |
| Items supplied | | lock nuts: 2 | |
| **Remarks** | | | |
| Pack quantity | | 1 pcs. | |

**Electrical connection - plug**

Connector: 1 x M12; coding: A; Contacts: gold-plated



# IGT247

## Inductive full-metal sensor

**IGK3005-BPKG/AM/US-104**

## Connection

