


E10108



Kabelkompatibelt støpsel

SDOAH040PLSFKPG



Elektriske data

Driftsspenning	[V]	< 250,00 AC
----------------	-----	-------------

Driftsforhold

Omgivelsestemperatur	[°C]	-40,00...85,00
Beskyttelse		IP 67

Mekaniske data

Vekt	[g]	15,20
Dimensjoner	[mm]	36,00 x 20,00 x 30,00
Materialer		PBT
Støpt kroppsmateriale		PBT
Materiale mutter		PA

Merknader

Antall i forpakning		1,00 stk.
---------------------	--	-----------

E10108



Kabelkompatibelt støpsel

SDOAH040PLSFKPG

Elektrisk tilkobling

skrueterminaler: ...0,5 mm²; Kabelgjennomføringer: PG 7

Elektrisk tilkobling - Stikkontakter

Koblinger: 1 x M12, vinklet; koding: B; Støpt kropp: PBT; låse: PA



Tilkobling

