




Capacitive touch sensor

KTEEFOKMMFRKG/US/IO



Product characteristics		
Electrical design		PNP/NPN; (parameterisable)
Output function		normally open / normally closed; (parameterisable)
Communication interface		IO-Link
Housing		threaded type
Dimensions	[mm]	M22 x 1 / L = 39.7
Application		
Operating principle		dynamic; static; bistable; combination; (parameterisable)
Electrical data		
Operating voltage	[V]	8...32 DC
Protection class		III
Reverse polarity protection		yes
Current consumption		< 7,2 mA; (LED off: Ub = 24V)
		< 125 mA; (LED white, max. brightness: Ub = 8V)
		< 79 mA; (LED white, max. brightness: Ub = 12V)
		< 43 mA; (LED white, max. brightness: Ub = 24V)
		< 35 mA; (LED white, max. brightness : Ub = 32V)
Inputs		
Total number of inputs		2
Switching level high	[V]	< 4.8; (at 24V safely off : Voltage <= Ub*0,2)
Switching level low	[V]	> 19.2; (at 24V safely on : Voltage >= Ub*0,8)
Inputs		according to the standard IEC 61131-2 (Typ 3)
Outputs		
Electrical design		PNP/NPN; (parameterisable)
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	1.5



Capacitive touch sensor

KTEEFOKMMFRKG/US/IO

Permanent current rating of switching output DC [mA]	200
Short-circuit protection	yes
Overload protection	yes

Response times

Response time [ms]	64
--------------------	----

Software / programming

Parameter setting options	normally open / normally closed; PnP/nPnP; static; dynamic; bistable; combination; Switch-on and switch-off delay; brightness; Sensitivität; Operating conditions
---------------------------	---

Interfaces

Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1.3	
Profiles	Function class	Designation
	0x0002	Fixed Switching Sensor
	0x4000	Identification and Diagnosis
	0x8101	Locator
	0x8102	ProductURI
	0x800C	Sensor Control
Min. process cycle time [ms]	13.2	

Operating conditions

Ambient temperature [°C]	-30...65
Protection	IP 65; IP 67; IP 69K; (on the front)

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m / 3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	IEC 61000-6-3, EN 55011	(Class B)
	IEC 61000-4-5 Surge	1 kV (L+ to L- , 42 Ω, 0,5 μF) / 0,5 kV (all cables to L- , 42 Ω, 0,5 μF)
Vibration resistance	EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes
Shock resistance	EN 60068-2-27 Ea	50 g 11 ms half-sine; 20 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance	EN 60068-2-29 Eb	40 g 6 ms half-sine; 8000 shocks each in every direction of the 3 coordinate axes
MTTF [years]	218	

Mechanical data

Weight [g]	48.4
Housing	threaded type
Dimensions [mm]	M22 x 1 / L = 39.7
Thread designation	M22 x 1
Materials	housing: PA; lock nut: PBT

Displays / operating elements

Display	operation	LED, RGB configurable
---------	-----------	-----------------------

KTE101



Capacitive touch sensor

KTEEFOKMMFRKG/US/IO

Accessories	
Items supplied	lock nuts: 1
	transparent symbol disc: 1
	symbol sticker: 1
Accessory required	symbol disc
Remarks	
Pack quantity	1 pcs.
Electrical connection	

Connector: 1 x M12; coding: A

