


Welding adapter for process sensors

WELDING ADAPT D50/G1



- 1 G1 internal thread Aseptoflex Vario
2 sealing area

ACS EC 1935/2004 EHEDG Tested  Reg31

Application

Installation	for thin wall thicknesses
Pressure rating [bar]	50
Note on pressure rating	for the connection sensor - adapter

Tests / approvals

Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.

Mechanical data

Weight [g]	191.5
Materials (wetted parts)	stainless steel (316L/1.4435) ; surface characteristics : Ra<0,4 / Rz 4
Sensor connection	G 1 internal thread Aseptoflex Vario
Process connection	welding adapter Ø 50 mm
Sealing	Gasket

Accessories

Items supplied	O-rings: 1 x 24 x 2, EPDM, FDA compliant, E30054
Accessories (optional)	O-ring: 1 x 24 x 2, FKM, FDA compliant, E30123

Remarks

Pack quantity	1 pcs.
---------------	--------