




Inductive sensor

IFG3007-BPKG/5M



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	7
Housing	cylindrical
Dimensions [mm]	Ø 11 / L = 38

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	400
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	7
Real sensing range S_r [mm]	$7 \pm 10 \%$
Operating distance [mm]	0...5.7

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of S_r]	1...15
Switch point drift [% of S_r]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

IF6023



Inductive sensor

IFG3007-BPKG/5M


MTTF	[years]	2744
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	power supply	Class 2
	File number UL	E174191

Mechanical data		
Weight	[g]	198.5
Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 11 / L = 38
Materials		PBT

Displays / operating elements		
Display	switching status	1 x LED, yellow

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Cable: 5 m, PVC; 3 x 0.34 mm²		
Connection		



	Core colours :
BK =	black
BN =	brown
BU =	blue